

Customer Release Notes

Xerox AltaLink C80XX Series

Release Version 100.xxx.057.09608

RELEASE DATE OCTOBER 2, 2017

dc17rn3671

Software Release Details

Product	Software Version
Xerox® AltaLink® C8030/C8035	100.001.057.09608
Xerox® AltaLink® C8045/C8055	100.002.057.09608
Xerox® AltaLink® C8070	100.003.057.09608

Purpose

THIS FIRMWARE RELEASE CONTAINS FIXES ADDED SINCE VERSION 100.XXX.057.09603

- Image Quality improvements when using Postscript print driver, with print quality setting in the default or “standard” mode
 - improvement in print quality addressing light and/or washed out prints
 - color reproduction updated to be more consistent with print quality settings in “enhanced” mode
- Image Quality improvements when using PCL print driver , with print quality setting in the default or “standard” mode
 - improvement in print quality addressing light halftone details and/or washed out prints
 - improved color balance, consistency and reproduction
- Image Quality improvements when Copying
 - improvements to reproduction of highlight areas and reduction in oversaturation in mid-tones
 - improved color reproduction
- Scan Image Quality improvements
 - Improved color reproduction and capture of highlights when scanning to Email, USB, Workflow Scanning, etc
- Card Reader Notification pop-up message
 - Eliminated card reader pop-up message, “Card Reader Detected”, after waking up from power saver/sleep mode
- Secure Print/Held Jobs
 - Resolved intermittent issue where secure print or held jobs are not visible at the local UI (however are visible on device web page)
- Provides fixes to address 319-409 faults

If further adjustment of Image Quality is needed to customize the output for your specific jobs, additional information can be found at: [Xerox® AltaLink® C80XX Series Color Multifunction Printer User Guide](#)

Or visit our Support pages on Xerox.com for more information